



General Purpose Handheld Area Imager Bar Code Readers for the Healthcare Industry

The key mission of scanners in the healthcare industry is to improve the quality of patient care while reducing medication errors. Additionally, healthcare environments have requirements that scanners need to be regularly cleaned and disinfected. The Datalogic Gryphon™ HC product series is specifically developed for healthcare applications with Disinfectant-Ready enclosures treated with anti-microbial additives and are designed to withstand daily cleaning with harsh disinfectant solutions.

The Gryphon™ 4400-HC 2D readers can decode virtually any 1D and 2D bar code symbology and can read codes from LCD monitors, cell phones, smartphones and other mobile devices. Enhanced optics offer improved motion tolerance and high speed imaging to read fast moving codes as well as the ability to capture images such as signatures, complete IDs or prescriptions.

Ideally suited for stationary applications in administration, laboratory and hospital environments, the GD4400-HC 2D desktop

model offers an affordable corded solution, while the GBT4400-HC 2D cordless model features the latest Class 2 Bluetooth® wireless technology.

Unique to the Gryphon 4400 series is Datalogic's exclusive Motionix™ motion-sensing technology which intuitively synchronizes the scanner with the user's actions allowing seamless transitions between handheld and hands-free style reading. When the device is in your hand, it's in handheld mode; when the device is still, it's in presentation mode. It's that simple.

The deep-red illumination of the Gryphon 4400 2D imagers eliminate the irritating 'flicker effect' found in competing products, allowing for comfortable all-day usage. The highly visible 4-Dot aimer provides a clear indication of the reading area, making targeting codes quick and easy. Datalogic's patented 'Green Spot' technology provides additional visual good-read confirmation which is ideal for quiet environments like bedside patient care. Datalogic Aladdin™ configuration software and Remote Host Management software provide simple tools to manage deployed devices and keep them synchronized across an enterprise.



All Products

- Disinfectant-Ready enclosures treated with anti-microbial additives
- Motionix™ motion-sensing technology for seamless reading mode transitions
- Omnidirectional reading of 1D, 2D and postal codes plus stacked and composite codes
- Extremely snappy reading performance
- Extended reading distances
- Advanced motion tolerance optics
- Highly visible 4-Dot aimer with center cross for targeted scanning
- Image capture and document scanning capabilities
- Datalogic's patented 'Green Spot' technology for good-read feedback
- USB Certified Kits Available

Cordless Products

- Bluetooth® Wireless Technology with up to 30 m / 98 ft range
- Batch Mode capability: >1200 codes stored in memory
- Point-to-point / Point-to-multipoint transmission
- Datalogic's unique patented 2-position cradle with 'Scan-While-Charging' capability
- Long lasting user-replaceable Lithium-Ion battery

www.scanning.datalogic.com



GRYPHON™ I 4400-HC 2D SERIES

Specifications

DECODING CAPABILITY

1D / LINEAR CODES

2D CODES

POSTAL CODES

STACKED CODES

ELECTRICAL

CURRENT

INPUT VOLTAGE

ENVIRONMENTAL

AMBIENT LIGHT
DROP RESISTANCE

ESD PROTECTION (AIR DISCHARGE)
HUMIDITY (NON-CONDENSING)
PARTICULATE AND WATER SEALING
TEMPERATURE

INTERFACES

PHYSICAL CHARACTERISTICS

COLORS AVAILABLE
DIMENSIONS
ENCLOSURE

WEIGHT

READING PERFORMANCE

IMAGE CAPTURE
IMAGER SENSOR
LIGHT SOURCE
MOTION TOLERANCE
PRINT CONTRAST RATIO (MINIMUM)
READING ANGLE
READING INDICATORS

RESOLUTION (MAXIMUM)

READING RANGES

TYPICAL DEPTH OF FIELD

SAFETY & REGULATORY

AGENCY APPROVALS

ENVIRONMENTAL COMPLIANCE
LASER CLASSIFICATION

UTILITIES

DATALOGIC ALADDIN™

OPOS / JAVAPOS

REMOTE HOST DOWNLOAD

WARRANTY

Gryphon™ I GD4400-HC 2D

Autodiscriminates all standard 1D codes including GS1 DataBar™ linear codes
Aztec Code; China Han Xin Code; Data Matrix;
MaxiCode; Micro QR Code; QR Code
Australian Post; British Post; China Post; IMB; Japanese Post; KIX Post; Korea Post; Planet Code; Postnet; Royal Mail Code (RM4SCC)
EAN/JAN Composites; GS1 DataBar Composites; GS1 DataBar Expanded Stacked; GS1 DataBar Stacked;
GS1 DataBar Stacked Omnidirectional; MacroPDF; MicroPDF417; PDF417; UPC A/E Composites

Operating (Typical): 160 mA @ 5 VDC; Standby/Idle (Typical): 65 mA @ 5 VDC
4.2 - 5.25 VDC

0 - 100,000 lux
Withstands repeated drops from 1.5 m / 5.0 ft onto a concrete surface
16 kV
5 - 90%
IP52
Operating: 0 to 50 °C / 32 to 122 °F
Storage/Transport: -20 to 70 °C / -4 to 158 °F

RS-232 / USB / Keyboard Wedge / Wand Multi-Interface

Light Green/Light Grey (Rubber/Plastic)
18.1 x 7.1 x 10.0 cm / 7.1 x 2.8 x 3.9 in
Disinfectant-Ready Enclosure Treated with Anti-Microbial Additives
195.0 g / 6.9 oz

Graphic Formats: BMP, JPEG, TIFF; Greyscale: 256, 16, 2
Wide VGA: 752 x 480 pixels
Aiming: 650 nm VLD
25 IPS
25%
Pitch: +/- 40°; Roll (Tilt): 180°; Skew (Yaw): +/- 40°
Beeper (Adjustable Tone); Datalogic 'Green Spot'
Good Read Feedback; Good Read LED
1D Linear: 0.102 mm / 4 mils; Data Matrix: 0.178 mm / 7 mils; PDF417: 0.102 mm / 4 mils

Minimum distance determined by symbol length and scan angle.
Printing resolution, contrast, and ambient light dependent.

Code 39: 5 mils: 4.0 to 19.0 cm / 1.6 to 7.5 in
Code 39: 10 mils: 1.0 to 30.0 cm / 0.4 to 11.8 in
Data Matrix: 10 mils: 2.0 to 16.0 cm / 0.8 to 6.3 in
Data Matrix: 15 mils: 0 to 23.6 cm / 0 to 9.3 in
EAN-13: 13 mils: 1.5 to 40.0 cm / 0.6 to 15.7 in
PDF417: 10 mils: 0.5 to 22.0 cm / 0.2 to 8.6 in
QR Code: 10 mils: 3.0 to 12.5 cm / 1.2 to 4.9 in

The product meets necessary safety and regulatory approvals for its intended use.

The Quick Reference Guide for this product can be referred to for a complete list of certifications.
Complies to China RoHS; Complies to EU RoHS
Caution Laser Radiation - Do not stare into beam;
IEC 60825 Class 2

Datalogic Aladdin configuration program is available for download at no charge.

JavaPOS Utilities are available for download at no charge.

OPOS Utilities are available for download at no charge.
Lowers service costs and improves operations.

5-Year Factory Warranty

Accessories

All Products



Mounts/Stands

- 11-0362: Holder, Multi-Purpose, Grey
- HLD-G040-WH: Desk/Wall Holder, G040, White
- STD-AUTO-G040-WH: Smart Stand, G040, White
- STD-G040-WH: Basic Stand, G040, White

Specifications

CORDLESS COMMUNICATIONS

DECODING CAPABILITY

1D / LINEAR CODES

2D CODES

POSTAL CODES

STACKED CODES

ELECTRICAL

BATTERY

CRADLE INDICATOR LEADS

CURRENT

INPUT VOLTAGE

ENVIRONMENTAL

AMBIENT LIGHT
DROP RESISTANCE

ESD PROTECTION (AIR DISCHARGE)
HUMIDITY (NON-CONDENSING)
PARTICULATE AND WATER SEALING
TEMPERATURE

INTERFACES

PHYSICAL CHARACTERISTICS

COLORS AVAILABLE
DIMENSIONS

ENCLOSURE

WEIGHT

READING PERFORMANCE

IMAGE CAPTURE
IMAGER SENSOR
LIGHT SOURCE
MOTION TOLERANCE
PRINT CONTRAST RATIO (MINIMUM)
READING ANGLE
READING INDICATORS

RESOLUTION (MAXIMUM)

READING RANGES

TYPICAL DEPTH OF FIELD

SAFETY & REGULATORY

AGENCY APPROVALS

ENVIRONMENTAL COMPLIANCE
LED CLASSIFICATION

UTILITIES

DATALOGIC ALADDIN™

OPOS / JAVAPOS

WARRANTY

Gryphon™ I GBT4400-HC 2D

Bluetooth Wireless Technology

Piconet: Max. Readers per Radio Receiver: 7 (when using an external Piconet dongle); Profiles: SPP (Serial Port Profile) Protocol: Bluetooth 2.0 Certified Class 2
Radio Frequency: 2.4 GHz
Radio Range (Open Air): 30.0 m / 98.4 ft; Range distances are measured using the base station. Range with connection to other Bluetooth peripherals may show different results.
Security: Data Encryption; Scanner Authentication

Autodiscriminates all standard 1D codes including GS1 DataBar™ linear codes
Aztec Code; China Han Xin Code; Data Matrix; MaxiCode; QR Code
Australian Post; China Post; IMB; Japanese Post; KIX Post; Korea Post; Planet Code; Postnet; Royal Mail Code (RM4SCC)
EAN/JAN Composites; GS1 DataBar Composites;
GS1 DataBar Expanded Stacked; GS1 DataBar Stacked;
GS1 DataBar Stacked Omnidirectional; MacroPDF;
MicroPDF417; PDF417; UPC A/E Composites

Battery Type: Lithium-Ion, 2100 mAh; Charge Time: External Power: 4 Hours @ 12 VDC; Reads per Charge: 50,000
Battery Charging (Red); Charge Completed (Green); Power/Data (Yellow)
Charging (Typical): < 8 W; Operating (Typical): < 2.5 W @ 5 VDC; Standby/Idle (Typical): < 2.5 mA @ 5 VDC
4.5 - 14.0 VDC +/- 5%

100,000 lux
Withstands repeated drops from 1.5 m / 5.0 ft onto a concrete surface
16 kV
0 - 95%
IP52
Operating: 0 to 50 °C / 32 to 122 °F
Storage/Transport: -20 to 70 °C / -4 to 158 °F
RS-232 / USB / Keyboard Wedge / Wand Multi-Interface

Light Green/Light Grey (Rubber/Plastic)
Cradle: 18.6 x 9.9 x 5.6 cm / 7.25 x 3.9 x 2.2 in
Reader: 18.1 x 7.1 x 10.0 cm / 7.1 x 2.8 x 3.9 in
Disinfectant-Ready Enclosure Treated with Anti-Microbial Additives
Cradle: 246.0 g / 8.68 oz; Reader: 245.0 g / 8.64 oz

Graphic Formats: BMP, JPEG, TIFF; Greyscale: 256, 16, 2
Wide VGA: 752 x 480 pixels
Aiming: 650 nm VLD
25 IPS
25%
Pitch: +/- 40°; Roll (Tilt): 360°; Skew (Yaw): +/- 40°
Beeper (Adjustable Tone); DataLogic 'Green Spot' Good Read Feedback; Good Read LED
1D Linear: 0.102 mm / 4 mils; Data Matrix: 0.178 mm / 7 mils;
PDF417: 0.127 mm / 5 mils

See Chart for GD4400-HC 2D

The product meets necessary safety and regulatory approvals for its intended use.
The Quick Reference Guide for this product can be referred to for a complete list of certifications.
Complies to China RoHS; Complies to EU RoHS
Caution Laser Radiation - Do not stare into beam;
IEC 60825 Class 2

DataLogic Aladdin configuration program is available for download at no charge
JavaPOS Utilities are available for download at no charge.
OPOS Utilities are available for download at no charge.
3-Year Factory Warranty

Accessories

Cordless Products



Base Stations/Chargers

- BC4030-HC-BT: Base/Charger Standard Multi-Interface, Healthcare
- CHR-GM40-WT: Charging Only Base Station, White

Batteries/Battery Chargers

- RBP-GM40 Removable Battery Pack

Datalogic Scanning's Disinfectant-Ready Enclosures for Healthcare

Datalogic Scanning offers bar code readers designed specifically for the healthcare industry with Disinfectant-Ready enclosures treated with anti-microbial additives that can help fight against the spreading of germs. This is particularly important if the scanner is traveling room-to-room on a medication cart with a nurse. The Disinfectant-Ready enclosures can withstand daily cleaning with harsh chemical cleaning solutions commonly used in a healthcare environment.

PRODUCT	CHEMICAL CONTENT
Sani-Cloth® HB, Sani-Cloth® Plus, Super Sani-Cloth®	Quaternary Ammonium Chloride solution
Hepacide Quat II	Virucidal disinfectant cleaner
Alcohol Wipes	70% Isopropyl Alcohol
CaviWipes™	Isopropanol 10-20%; Ethylene Glycol Monobutyl Ether 1-5%
Virex® 256	n-Alkyl Dimethyl Benzyl Ammonium Chloride; Didecyl Dimethyl Ammonium Chloride
409® Glass and Surface Cleaner	n-Alkyl Dimethyl Benzyl Ammonium Chloride; n-Propoxypropanol
Windex® Blue	Isopropyl Alcohol
Clorox® Bleach	Sodium Hypochlorite; Sodium Hydroxide
100% Gentle dish soap and water	



MEDITECH



www.scanning.datalogic.com

The Bluetooth word mark and logos are owned by the Bluetooth SIG, Inc. and any use of such marks by Datalogic Scanning Inc. is under license. • The USB-IF Logos are trademarks of Universal Serial Bus Implementers Forum, Inc.

© 2011 Datalogic Scanning, Inc. • All rights reserved. • Protected to the fullest extent under U.S. and international laws. • Copying or altering of this document is prohibited without express written consent from Datalogic Scanning, Inc.

Datalogic and the Datalogic logo are registered trademarks of Datalogic S.p.A. in many countries including the U.S.A. and the E.U. • Datalogic Aladdin is a trademark of Datalogic Scanning Group S.r.l. • Gryphon and Motionix are trademarks of Datalogic Scanning, Inc. • Other brand and product names may be trademarks of their respective owners.

Product specifications are subject to change without notice.

DS-GRYPHON4400-HC2D-EN REV A 20110516