

## **Quick Check® On-Line**SV Series Verifiers



## Features

State-of-the Art Digital Signal Processor (DSP) Technology -Ensures higher processing speed, faster printers, and more analysis per symbol.

ANSI, Traditional, Encoded Data Format, and Laser Scanning Methods - Provide reflectance, dimensional, and format measurements.

QC ScanView Windows®-based Software for System Operation - Programmable and serial port outputs assist in setup.

Flexible Optical Configurations - More adaptable optics read higher density and low contrast symbols.

Datamatch Compatibility - Secures encoded data equivalence.

HHP's Quick Check® Model QCOLV-SV100 Verifier is a universal system component that can analyze linear bar code print quality, check encoded data, and detect system failures. In its basic mode of operation, the QCOLV-SV100 performs bar code verification and operates in various synchronous modes.

The QCOLV-SV100 combines state-of-the-art digital signal processor (DSP) technology, a proprietary high-speed moving beam laser scanner with unique analog output capability, and flexible I/O and communications capability. This powerful architecture enables the unit to be an economical Quality Assurance tool for practically any bar code printing, application, or conveyance system.

The QCOLV-SV100 performs most accepted methods of bar code verification: ANSI method, traditional method, encoded data format checks, and laser scanning type analyses. These wide ranging analysis parameters can be used to measure bar code quality and detect failure mechanisms for any print technology. Bar code quality and encoded data information can be reported through the serial communications port for each code analyzed; therefore, accountability for all printed bar codes is possible. The QCOLV-SV100 I/O consists of five programmable output ports, two programmable display LEDs, and a sync input. The programmable ports allow the unit to be used as a controller for pausing printers, activating lights, and gating conveyors.

The recommended setup tool for the QCOLV-SV100 is HHP's QC ScanView, Windows®-based software. This program simplifies setup via menus, and offers real time monitoring of bar codes being analyzed. QC ScanView programs the QCOLV-SV100 via serial communication using a PC download language (described in the User's Guide, part #QCOLVSV/UG).

**Upgrade your image.** 

## Quick Check® On-Line SV Series Verifiers

Dimensions

Height: 5.2 in. (13.2 cm) Width: 4.4 in. (11.2 cm) Depth: 2.4 in. (6.1 cm)

Mechanical/Electrical

**Communication Port:** DB-9, male, RS-232C, programmable baud rate up to 115,200 baud

I/O Power: DB-15, male, 5 programmable outputs, 2 sync inputs +5VDC @ 1 amp required 2 sets of mounting holes on 2 surfaces, or clamp for tightening to 3/8 in. (.5 mm) rod Mounting:

LEDs:

**Environmental** 

40 to 105° F (4 to 41° C) **Operating Temperature:** -4 to 140° F (-20 to 60°C) Storage Temperature: Relative Humidity: 10 to 95% Non-condensing

**Ambient Light:** Not to exceed .5 mW/sq-mm 600 nm to 700 nm (calculated at about 2% of laser light level; estimate, not verified)

MTBF: 10,000 hours (est.) (dominated by motor, then laser life)

Scanner

Scan Rate: 400 scans/second Laser Power: 3 mW (±.5 mW) 650-670 nm Wavelength: Beam Shape: Elliptical

Analysis Rate: 100 analyses/second (min.)

**Bar Code Density** 

X Dimension: 6.6 mil (.2 mm) min. to 40 mil (1 mm) max.

Scan Width: 6 inches (15.2 cm)

X Dimension: 10 mil (.25 mm) or larger; 4.5 in. (11.4 cm) - (x dimension <10 mil)

Depth of Field: ±.125 in. (3.2 mm) min. with all verification analysis enabled

**Symbologies** EAN/UPC with addenda, Code 39, Interleaved 2 of 5, Codabar, Code 128, Code 93

**Operation Modes** 

Sync Mode

**Moving Bar Codes:** 

A sync signal is used to indicate when an object or label containing a bar code has entered or exited the laser beam. Bar codes are analyzed, ports activated, and transmissions sent as the bar codes pass through the beam. The QCOLV-SV100 is programmed for the number of bar codes to expect during a sync period. Therefore, the QCOLV-SV100 detects missing or undetectable bar codes. A hardware

input is the most common sync source for Sync Mode.

Sync Mode

Stationary Bar Codes:

Bar codes are placed in the beam and held in a known position. A sync input commands the unit to turn on the laser beam, perform a programmable number of scans, report the analysis, and turn off the laser beam. RS-232 communication sync command (-SA) is the most

A sync signal is not used and the unit scans and analyzes bar codes as they pass through the laser beam. This mode is only recommended

common sync source. A rastering laser option is often used to analyze the bar code area.

Non Sync Mode Free Scan Operation:

if the QCOLV-SV100 is used as a bar code decoder, since it can't report missing or undetectable bar codes. Parameters Analyzed

Average Bar Deviation (Traditional method parameter) Minimum Bar Deviation (Traditional method parameter)

Maximum Bar Deviation (Traditional method parameter) PCS (Traditional method parameter)

Reflectance - Light (Traditional method parameter) Reflectance - Dark (Traditional method parameter)

Ratio (Traditional method parameter) Quiet Zone (Traditional method parameter) X Dimension (Traditional method parameter) **Decodability** (ANSI method parameter) **Defects** (ANSI method parameter)

Edge Contrast (ANSI method parameter) Global Threshold (ANSI method parameter) Modulation (ANSI method parameter)

Safety/Regulatory FCC Class B, CE Certified

Windows is a registered trademark of Microsoft Corporation in the United States and/or other countries.

Overall Symbol Grade (ANSI method parameter) Reference Decode (ANSI method parameter)

Rmin/Rmax (ANSI method parameter) Symbol Contrast (ANSI method parameter) Bar Code Direction (scanner decoder function) Encoded Data (scanner decoder function)

Symbology Type (scanner decoder function) % Decode (multiple scanning parameter)

Modulo Check Digits (mandatory symbology and optional

application parameters)

Worldwide Offices

Offices Serving North America Skaneateles Falls, NY Tel: +1 315 685 8945

or, in North America: +1 800 782 4263

sales@hhp.com Charlotte, NC Tel: +1 704 998 3998 or, in North America: +1 800 782 4263

sales@hhp.com

Offices Serving Europe, Middle East, and Africa

Europe Tel: +31 (0) 40 29 01 600 euro sales@hhp.com United Kingdom
Tel: +44 (0) 1 925 240055
euro\_sales@hhp.com

Tel: +353 (0) 502 44007 euro\_sales@hhp.com

France Tel: +33 (0) 1 461 04111 euro\_sales@hhp.com Germany Tel: +49 (0) 7 477 151377

euro\_sales@hhp.com Tel: +34 93 228 76 68 euro\_sales@hhp.com

Offices Serving Asia and the Pacific Rim

Hong Kong Tel: +852 2511 3050/2511 3132 asia\_sales@hhp.com Japan Tel: +813 52127392

asia\_sales@hhp.com

Offices Serving Latin America Naples, Florida Tel: +1 239 263 7600

la-sales@hhp.com S, o Paulo Tel: +55 11 5016 3454 la-sales@hhp.com Rio De Janiero Tel: +55 21 2494 7060 la-sales@hhp.com

Web Site Address www.hhp.com
Hand Held Products, Inc. d/b/a HHP (iHHPI) ©1999-2002. All rights reserved. Printed in the U.S.A.
Due to HHPIs continuing product improvement programs, specifications and features herein are subject to change without notice.