

ZEBRA CS4070-HC

THE POCKET-SIZED WIRELESS ENTERPRISE-CLASS 1D/2D SCANNER FOR CARTS AND MORE.

Put advanced bar code scanning in the pockets of your healthcare workers to improve patient safety and the patient experience.

Bar code scanning at patient bedside is crucial in preventing deadly errors in medication administration and specimen collection. Now, you can keep enterprise-class bar code capture at the fingertips of every nurse and lab technician with the CS4070-HC. This little wireless enterprise class bar code scanner is designed for the mission critical world of the healthcare worker. Small enough to be easily carried at all times, it can be tucked in a pocket or worn on a lanyard. Superior scanning technology means your healthcare workers can dependably scan any electronic or printed 1-D or 2-D bar code in any condition in the time it takes to press the scan button, whenever and wherever required. With the press of the dedicated pairing button, this flexible Bluetooth scanner is easily paired with in-room computers and workstations-on-wheels (WOWs) ' or even tablets. Add its rugged disinfectant-ready design that prevents the spread of germs, full shift power, user-selectable scanning feedback and superior ergonomics, and the CS4070-HC is the ideal individual scanning companion for your healthcare workers.

PRZM Intelligent Imaging technology for next generation bar code scanning performance 'only from Zebra

Delivers laser-style speed and accuracy for first-time every time split second capture of 1D and 2D printed bar codes in virtually any condition 'even if they are dirty, scratched or poorly printed.

Scan virtually any bar code on any medium

Scans 1-D, 2-D and PDF417 bar codes displayed on a screen or printed on paper labels, as well as the tiny bar codes printed on individual medication doses and bar codes on curved, reflective surfaces, such as vials, syringes, IV bags, suppositories and patient wristbands.

Superior ergonomics

One of the smallest and lightest devices in its class, the CS4070-HC can be tucked in a pocket or worn around the neck on a lanyard. Grooves guide the hand to the most comfortable placement and provide a secure grip, and the placement of trigger buttons enables effortless scanning with any size hand.

Connect with one simple scan

Healthcare workers can connect the CS4070-HC to a workstation-on-wheels (WOW) or thin client by simply scanning a barcode on the CS4070-HC Bluetooth dongle accessory.

Withstands constant disinfecting

IP52 sealing and a specially designed disinfectant-ready plastic housing allow safe wipe-down with a wide variety of harsh chemicals to help prevent the spread of germs.

Durable design 'built to be dropped

Operates reliably after 5 ft./1.2 m drops and 500 consecutive 'tumbles' from 1.64 ft./0.5 m.



APPLICATIONS

- Medication administration
- Blood product administration
- Specimen labeling
- Specimen tracking
- Medication tracking at the dose level in the hospital pharmacy
- Inventory takes in individual floor supply cabinets for timely replenishment

One million+ scans for superior value

Since healthcare workers need to scan frequently, the scan button is tested to handle over a million presses.

Full-shift power 'period

In the mission-critical world of healthcare, users count on full-shift operation. That's why the field replaceable battery can be easily changed on-the-go and is designed to last an entire busy 12-hour shift, with an LED indicator that alerts the user when a battery change is needed.

Day and night 'do-not-disturb' modes

Healthcare workers can choose to mix and match the decode feedback that is right for the moment: visual (green light /red light), haptic (vibration) and an audible tone.

Point-and-shoot scanning simplicity

Bar code capture is easy. An extraordinarily wide working range combined with omnidirectional scanning eliminates the need to align scanner and bar code ' no need to disturb a sleeping patient to capture the bar code on a wristband.

With Service from the Start Advance Exchange with Comprehensive Coverage, your CS4070-HC scanners are covered 'period.

This optional service plan keeps devices up, running and in like-new condition with coverage for accidental damage and everyday wear-and-tear 'all for just pennies a day.

GIVE YOUR HEALTHCARE WORKERS THE POCKETABLE 1D/2D BAR CODE SCANNING THEY NEED TO IMPROVE PATIENT SAFETY- AND THE PATIENT EXPERIENCE.

For more information, visit www.zebra.com/cs4070hc or access our global contact directory at www.zebra.com/contact

CS4070-HC SPECIFICATIONS CHART

PHYSICAL CHARACTERISTICS		USER ENVIRONMENT (CONTINUED)	
Dimensions	4.39 in. L x 1.79 in. W x 1.02 in. H 11.15 cm L x 4.55 cm W x 2.6 cm H	Ambient Lighting Tolerance	Tolerant to typical artificial indoor and natural outdoor (direct sunlight) lighting conditions. Fluorescent,
Weight	With batteries: 3.28 oz./93.2 g		Incandescent, Mercury Vapor, Sodium Vapor, LED1: 450 ft.
Scan Engine	SE4710 image engine	candles (4,844 Lux) Sunlight: 8,000 ft. candles (86,111 Lux)	candles (4,844 Lux) Sunlight:
Memory	512 MB Flash		8,000 ft. candles (86,111 Lux)
Memory Capacity	Over 1 million barcodes (UPC with time date stamp)	BLUETOOTH	
LEDs	Scan LED (Green, Red, and Amber) and Bluetooth® LED (Blue) Four LED battery status indicator	Bluetooth Radio	Bluetooth, Class 1/Class 2, Version 2.1 + Enhanced Data Rate (EDR)
Buttons	Scan, remove scan (batch mode only), enable Bluetooth (RF scanners only), battery status; scan button tested to a million depressions, all other buttons tested to 250,000 depressions	Bluetooth Range	300 ft./100 m when configured for Class 1 or 30 ft./10 m when configured for Class 2
		Bluetooth Profiles	HID keyboard wedge and Serial Port Profile (SPP) and Wireless SS I (proprietary)
OPERATING MODES		ACCESSORIES	
Batch	Scans recorded with optional time/	BT-CS1-0BR Bluetooth Dongle for Bluetooth Class 1	

Open Bluetooth	date stamp Real time wireless data transmission	Version 2.0 enables connection to host by simply scanning a barcode; CHS5000-1000CR Charge Cradle charges one scanner and one battery simultaneously; CHS5000-8000CR Charge Cradle charges up to eight scanners; SAC5000-8000CR Charge Cradle charges up	
BATTERY		to eight batteries; lan	yard
Battery	950 mAh Lithium ion	REGULATORY	
Charge Time	3 hours 40 minutes	Laser Safety IEC62471:2006 (Ed.1.0); EN62471	
Power Consumption	Batch: 24 hours use or 8,500 scans (6 scans per minute on full charge) Standby: 3 months Bluetooth 12 hours use or 4,250 scans (6 scans per minute on full charge) 5V, 500mA max while charging	Laser Salety	:2008 (LED)
		EMC	FCC Part 15 Class B, ICES 003 Class B, EN 55022, EN 55024, EN 301 489- 1, EN 301 489-17
		Radio	EN 300 328
PERFORMANCE	E CHARACTERISTICS	Electrical Safety	UL 60950-1, C22.2 No. 60950-1, EN 60950-1,
Decode Capability	1D and 2D symbologies	IEC 60950-1	
Interfaces Supported	USB (micro jack): Bluetooth	Environmental	EN50581
Real Time Clock	A date/time stamp can be recorded	WARRANTY	
	with each bar code scanned (batch mode operation only)	Warranted against defects in workmanship and materials for a period of thirty-six (36) months	
Batch Communication	USB 2.0		
		DECODE RANGE	
USER ENVIRONMENT		4 mil Code 39:	2.9 in. / 7.4 cm ' 8.4 in. / 21.4 cm
Drop Specification	Multiple 5 ft./1.5 m drops to concrete	5 mil Code 128:	2.4 in. / 6.1 cm ' 7.8 in. / 19.8 cm
		5 mil 39:	1.6 in. / 4.1 cm ' 13.1 in. / 33.3 cm
Tumble Specification	250 cycles @ 1.64 ft./0.5 m (500 drops)	5 mil PDF417:	2.7 in. / 6.9 cm ' 8.0 in. / 20.3 cm
Sealing	IP52, disinfectant ready	10 mil Data Matrix:	2.5 in. / 6.4 cm ' 9.7 in. / 24.7 cm
Operating Temperature	32° to 104° F/0° to 40° C	100% UPCA:	1.4 in. / 3.6 cm* ' 25.6 in. / 65.0 cm
		20.0 mil Code 39:	1.6 in. / 4.1 cm* ' 29.6 in. / 75.2 cm
Storage Temperature	-40° to 158° F/-40° to 70°C	*Minimum distance determined by symbol length and scan angle	
Humidity	10 to 95% noncondensing	SERVICES	

SERVICES

Enjoy easy access to fast repair and expert support with Service from the Start. Add 'next business day' replacement with Advanced Exchange.





Part number: SS -CS4070HC. Printed in USA 04/15.©2015 ZIH Corp. ZEBRA, the Zebra head graphic and Zebra Technologies logo are trademarks of ZIH Corp, registered in many jurisdictions worldwide. All rights reserved. All other trademarks are the property of their respective owners.

ZEBRA TECHNOLOGIES